










# Hira Tech Screw Drivers Guidance

| SIZE                                                                                               | IMPLANT SYSTEM                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         | RECOMMENDED TORQUE |
|----------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------|
|  <b>Ball Torx</b> | 1. Most of angled screws of HIRA TECH Ti-base (screw head size should be more than 2.1 mm)                                                                                                                                                                                                                                                                                                                                                                                                             | 15 Ncm             |
|                                                                                                    | 2. ALL IMPLANT SYSTEM FOR DISK ANGULATED SCREW CHANNELS                                                                                                                                                                                                                                                                                                                                                                                                                                                |                    |
|  <b>Ball Hex</b>  | Some of angled screws of HIRA TECH Ti-base (screw head size should be less than 2.1 mm)                                                                                                                                                                                                                                                                                                                                                                                                                | 15 Ncm             |
|                                                                                                    | *Please visit our website to see the list.                                                                                                                                                                                                                                                                                                                                                                                                                                                             |                    |
|  <b>Hex 1.0</b>   | DENTIUM® NR Line / DENTSPLY® Ankylos® C/X Implant etc.                                                                                                                                                                                                                                                                                                                                                                                                                                                 | 15 Ncm             |
|  <b>Hex 1.2</b>   | ADIN® TOUAREG™ S&OS / ANTHOGRY® anthofit® / BIOMET 3i® Certain® / BIOMET 3i® EXTERNAL HEX CONNECTION / BTI INTERNAL® / COWELLMEDI® INNO Internal / DENTIST® i-Clean / DENTSPLY® Xive® / DIO® UF / Global D® Tekka® In-Kone / MEGAGEN® / MEGAGEN® AnyONE / MEGAGEN® Anyridge® / MEGAGEN® Anyridge® Extra EZ POST / MEGAGEN® EZ Plus / MEGAGEN® Rescue / NEOBIOTECH® / OSSTEM® GS(TS) / OSSTEM® SS / OSSTEM® US / SHINHUNG® / SIC Invent® / SOUTHERN IMPLANTS MSC EXTERNAL HEX / WARANTEC® Oneplant etc. | 20 Ncm             |
|  <b>Hex 1.25</b>  | BEGO® / BIOHORIZONS® External® / BIOHORIZONS® Internal® / DENTIST® s-Clean / LASAK Bioniq® etc.                                                                                                                                                                                                                                                                                                                                                                                                        | 30 Ncm             |
|  <b>Hex 1.27</b> | Alpha-Bio Tec® Internal Hex / ANTHOGRY® axiom® / ASTRA TECH™ OsseoSpeed™ TX / CAMLOG® / CAMLOG® CONELOG® / CORTEX™ / DEEP® / DENTIUM® SimpleLine / DENTIUM® SuperLine / EBI® / IMPLANT DIRECT® Legacy™ / MIS® C1 / MIS® Internal Hexagon / ZIMMER® / ZIMMER® Spline A / ZIMMER® Spline B / ZIMMER® Tapered Screw-Vent® Sweden & Martina etc.                                                                                                                                                           | 30 Ncm             |
|  <b>Hex 1.3</b> | ASTRA TECH™ OsseoSpeed™ EV / CLC Conic / DYNA Pushin Octalock® / KENTEC® / PLATON® Type IV Pro / etc.                                                                                                                                                                                                                                                                                                                                                                                                  | 30 Ncm             |
|  <b>Torx</b>    | STRAUMANN® Bone Level® / STRAUMANN® Conical Bone Level® / STRAUMANN® synOcta® etc.                                                                                                                                                                                                                                                                                                                                                                                                                     | 35 Ncm             |
|  <b>Torx</b>    | BREDENT Medical SKY® etc.                                                                                                                                                                                                                                                                                                                                                                                                                                                                              | 25 Ncm             |
|  <b>Torx</b>    | NEOSS Pro Active® etc.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 | 35 Ncm             |
|  <b>Torx</b>    | ADIN® CLOSEFIT™ / NOBEL BIO CARE® Active™ / NOBEL BIO CARE® Branemark® / NOBEL BIO CARE® Replace Select™ etc.                                                                                                                                                                                                                                                                                                                                                                                          | 35 Ncm             |
|  <b>Cross</b>   | THOMMEN SPI® etc.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      | 30 Ncm             |